

Product data sheet

Characteristics

279C16EH-GY

GLAND STRAIGHT HOSE LOCK NUT



Main

Colour	Grey
Product brand	Clipsal
Range of product	Series 279C
Tool type	24 mm wrench

Complementary

Colour code	GY
Thread type	M16
Threaded length	1.5 mm
Cable outer diameter	16 mm
Material	PVC (polyvinyl chloride)
Device composition	Lock nut
Installation direction	Straight

Environment

Ambient air temperature for operation	-15...65 °C
---------------------------------------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	8 g
Package 1 Height	29 mm
Package 1 width	36 mm
Package 1 Length	53 mm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	0.112 kg
Package 2 Height	6.8 cm
Package 2 width	8.4 cm
Package 2 Length	10.8 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	250
Package 3 Weight	3.025 kg
Package 3 Height	25 cm
Package 3 width	21.4 cm
Package 3 Length	33.8 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile