

## Product data sheet

### Characteristics

## 279C20EH-GY

Clipsal - Cable Management, Flexible Electrical  
Hose Fittings, Straight Glands, 20mm



### Main

|                  |              |
|------------------|--------------|
| Colour           | Grey         |
| Product brand    | Clipsal      |
| Range of product | Series 279C  |
| Tool type        | 27 mm wrench |

### Complementary

|                        |                          |
|------------------------|--------------------------|
| Colour code            | GY                       |
| Thread type            | M20                      |
| Threaded length        | 1.5 mm                   |
| Cable outer diameter   | 20 mm                    |
| Material               | PVC (polyvinyl chloride) |
| Device composition     | Lock nut                 |
| Installation direction | Straight                 |

### Environment

|                                       |             |
|---------------------------------------|-------------|
| Ambient air temperature for operation | -15...65 °C |
|---------------------------------------|-------------|

### Packing Units

|                              |      |
|------------------------------|------|
| Unit Type of Package 1       | PCE  |
| Number of Units in Package 1 | 1    |
| Package 1 Height             | 3 cm |
| Package 1 Width              | 3 cm |
| Package 1 Length             | 4 cm |
| Package 1 Weight             | 14 g |

### Offer Sustainability

|                          |                                                                                                                                                                                      |
|--------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status | Green Premium product                                                                                                                                                                |
| REACH Regulation         |  <a href="#">REACH Declaration</a>                                                                |
| REACH free of SVHC       | Yes                                                                                                                                                                                  |
| EU RoHS Directive        | Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free   | Yes                                                                                                                                                                                  |
| Mercury free             | Yes                                                                                                                                                                                  |
| China RoHS Regulation    |  <a href="#">China RoHS Declaration</a>                                                           |

|                            |                                                                                      |
|----------------------------|--------------------------------------------------------------------------------------|
| RoHS exemption information |  Yes |
| Circularity Profile        | No need of specific recycling operations                                             |