

## Product data sheet

### Characteristics

# 279C20HF-BK

## Corrugated Fittings, HFT, Straight Glands

### Black, 20mm



#### Main

Colour	Black
Product brand	Clipsal
Range of product	Series 279C
Tool type	27 mm wrench

#### Complementary

Colour code	BK
Thread type	M20
Threaded length	1.5 mm
Cable outer diameter	20 mm
Material	PVC (polyvinyl chloride)
Device composition	Lock nut
Installation direction	Straight




#### Environment

Ambient air temperature for operation	-15...65 °C
---------------------------------------	-------------

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.7 cm
Package 1 Width	3.3 cm
Package 1 Length	3.3 cm
Package 1 Weight	12.0 g

#### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>

---

RoHS exemption information

 [Yes](#)

---

Environmental Disclosure

 [Product Environmental Profile](#)

---