

## Product data sheet

### Characteristics

# 279C20HF-BK

## GLAND STRAIGHT HFT LOCK NUT



### Main

Colour	Black
Product brand	Clipsal
Range of product	Series 279C
Tool type	27 mm wrench

### Complementary

Colour code	BK
Thread type	M20
Threaded length	1.5 mm
Cable outer diameter	20 mm
Material	PVC (polyvinyl chloride)
Device composition	Lock nut
Installation direction	Straight

### Environment

Ambient air temperature for operation	-15...65 °C
---------------------------------------	-------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	12 g
Package 1 Height	37 mm
Package 1 width	33 mm
Package 1 Length	33 mm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>