

Product data sheet

Characteristics

279C25EH-GY

Clipsal - Cable Management, Flexible Electrical
Hose Fittings, Straight Glands, 25mm



Main

Colour	Grey
Product brand	Clipsal
Range of product	Series 279C
Tool type	35 mm wrench

Complementary

Colour code	GY
Thread type	M25
Threaded length	1.5 mm
Cable outer diameter	25 mm
Material	PVC (polyvinyl chloride)
Device composition	Lock nut
Installation direction	Straight


Environment

Ambient air temperature for operation	-15...65 °C
---------------------------------------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.0 cm
Package 1 Width	4.0 cm
Package 1 Length	4.0 cm
Package 1 Weight	25.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration

RoHS exemption information

 [Yes](#)

Environmental Disclosure

 [Product Environmental Profile](#)
