

## Product data sheet

### Characteristics

# 279C32EH-GY

Clipsal - Cable Management, Flexible Electrical  
Hose Fittings, Straight Glads, 32mm



### Main

Colour	Grey
Product brand	Clipsal
Range of product	Series 279C
Tool type	46 mm wrench

### Complementary

Colour code	GY
Thread type	M32
Threaded length	1.5 mm
Cable outer diameter	32 mm
Material	PVC (polyvinyl chloride)
Device composition	Lock nut
Installation direction	Straight

### Environment

Ambient air temperature for operation	-15...65 °C
---------------------------------------	-------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	5.5 cm
Package 1 Length	4.5 cm
Package 1 Weight	0.05 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	10.6 cm
Package 2 Width	10.2 cm
Package 2 Length	14 cm
Package 2 Weight	0.302 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	21 cm
Package 3 Width	34.8 cm
Package 3 Length	44.5 cm
Package 3 Weight	6.425 kg

## Offer Sustainability

EU RoHS Directive

Not applicable, out of EU RoHS legal scope