

## Product data sheet

### Characteristics

# 279C32HF-BK

## GLAND STRAIGHT HFT LOCK NUT



### Main

Colour	Black
Product brand	Clipsal
Range of product	Series 279C
Tool type	46 mm wrench

### Complementary

Colour code	BK
Thread type	M32
Threaded length	1.5 mm
Cable outer diameter	32 mm
Material	PVC (polyvinyl chloride)
Device composition	Lock nut
Installation direction	Straight

### Environment

Ambient air temperature for operation	-15...65 °C
---------------------------------------	-------------

### Packing Units

Package 1 Weight	0.050 kg
------------------	----------

### Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.