

Product data sheet

Characteristics

279C40EH-GY

Straight Gland, Clipsal - Cable Management, 40mm

Main

Colour	Grey
Product brand	Clipsal
Range of product	Series 279C
Tool type	55 mm wrench

Complementary

Colour code	GY
Thread type	M40
Threaded length	1.5 mm
Cable outer diameter	40 mm
Material	PVC (polyvinyl chloride)
Device composition	Lock nut
Installation direction	Straight

Environment

Ambient air temperature for operation	-15...65 °C
---------------------------------------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.6 cm
Package 1 Width	5.3 cm
Package 1 Length	5.3 cm
Package 1 Weight	52.8 g

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Circularity Profile	No need of specific recycling operations