

Product data sheet

Characteristics

279C40HF-BK

Clipsal - Cable Management, Corrugated Fittings - HFT, Straight Glands Black, 40mm



Main

| | |
|------------------|--------------|
| Colour | Black |
| Product brand | Clipsal |
| Range of product | Series 279C |
| Tool type | 55 mm wrench |

Complementary

| | |
|------------------------|--------------------------|
| Colour code | BK |
| Thread type | M40 |
| Threaded length | 1.5 mm |
| Cable outer diameter | 40 mm |
| Material | PVC (polyvinyl chloride) |
| Device composition | Lock nut |
| Installation direction | Straight |

Environment

| | |
|---------------------------------------|-------------|
| Ambient air temperature for operation | -15...65 °C |
|---------------------------------------|-------------|

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 0.001 kg |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.