

Product data sheet

Characteristics

279C40HF-BK

GLAND STRAIGHT HFT LOCK NUT



Main

Colour	Black
Product brand	Clipsal
Range of product	Series 279C
Tool type	55 mm wrench

Complementary

Colour code	BK
Thread type	M40
Threaded length	1.5 mm
Cable outer diameter	40 mm
Material	PVC (polyvinyl chloride)
Device composition	Lock nut
Installation direction	Straight

Environment

Ambient air temperature for operation	-15...65 °C
---------------------------------------	-------------

Packing Units

Package 1 Weight	0.001 kg
------------------	----------