

## Product data sheet

### Characteristics

# 279C50-GY

## Clipsal - Cable Management, Corrugated Fittings, Straight Glands, 50mm



### Main

Colour	Grey
Product brand	Clipsal
Range of product	Series 279C
Tool type	66 mm wrench

### Complementary

Colour code	GY
Thread type	M50
Threaded length	1.5 mm
Cable outer diameter	50 mm
Material	PVC (polyvinyl chloride)
Device composition	Lock nut
Installation direction	Straight

### Environment


Ambient air temperature for operation	-15...65 °C
---------------------------------------	-------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.0 cm
Package 1 Width	5.8 cm
Package 1 Length	7.2 cm
Package 1 Weight	76.0 g

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>

RoHS exemption information	 Yes
Circularity Profile	No need of specific recycling operations