

Product data sheet

Characteristics

279C50HF-BK

Corrugated Fittings - HFT, Straight Glands Black, 50mm



Main

Colour	Black
Product brand	Clipsal
Range of product	Series 279C
Tool type	66 mm wrench

Complementary

Colour code	BK
Thread type	M50
Threaded length	1.5 mm
Cable outer diameter	50 mm
Material	PVC (polyvinyl chloride)
Device composition	Lock nut
Installation direction	Straight

Environment

Ambient air temperature for operation	-15...65 °C
---------------------------------------	-------------

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	70 cm
Package 1 Width	58 cm
Package 1 Length	72 cm
Package 1 Weight	33.4 g