

Product data sheet

Characteristics

2D4P5IPV3B-BU

CABLE LAN CAT 5E -305 METRE



Main

Range of product	Titanium
Product brand	Clipsal
Colour	External sheath: blue

Complementary

Communication network category	5e
AWG gauge	AWG 24
Cable shielding type	UTP
Cable insulation material	PVC (polyvinyl chloride)
Material	Conductor: bare copper
Diameter	0.51 mm (conductor)
External diameter	5 mm
Length	305 m
Colour code	BU




Environment

Ambient air temperature for operation	75 °C
Flame retardance	CM
Standards	ANSI/TIA/EIA-568-B ISO/IEC 11801

Packing Units

Package 1 Weight	0.032 kg
Package 1 Height	0.372 mm
Package 1 width	0.198 mm
Package 1 Length	0.368 mm

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	 RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation

 [China RoHS Declaration](#)

Environmental Disclosure

 [Product Environmental Profile](#)
