

Product data sheet

Characteristics

2F12CMIOR50

CBL FIB I/O 12MM OM3 RISER

Main

| | |
|------------------|------------|
| Product brand | Clipsal |
| Optic fiber type | Multi mode |
| Colour | Aqua |

Complementary

| | |
|----------------------|-----------|
| Optic fiber diameter | 50/125 µm |
| Fibre performance | OM3 |
| Diameter | 6.7 mm |
| Bending radius | >= 125 mm |
| Crush resistance | 600 N/m |

Packing Units

| | |
|------------------|----------|
| Package 1 Weight | 0.058 kg |
|------------------|----------|

Offer Sustainability

| | |
|--------------------------|--|
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| Environmental Disclosure |  Product Environmental Profile |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.