

Product data sheet

Characteristics

2F12S12MOLDN

CBL FIB L/T DC 12SM/12MM NY

Main

Product brand	Clipsal
Optic fiber type	Single mode
Colour	Aqua

Complementary

Optic fiber diameter	62.5/125 µm
Fibre performance	OM1
Diameter	9.1 mm
Bending radius	>= 180 mm
Crush resistance	1800 N/m