

## Product data sheet

### Characteristics

# 2F24CMOLDN

## CBL FIB L/T DC 24 MMNY

### Main

Product brand	Clipsal
Optic fiber type	Multi mode
Colour	Aqua

### Complementary

Optic fiber diameter	62.5/125 µm
Fibre performance	OM1
Diameter	9.2 mm
Bending radius	>= 180 mm
Crush resistance	1000 N/m

### Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Weight	0.07 kg