

Product data sheet

Characteristics

2F48CSOLDN

Clipsal Actassi, Optical Fibre Cable, Loose Tube, Dry Core, 48 Core, Single Mode Nylon

Main

Product brand	Clipsal
Optic fiber type	Single mode

Complementary

Fibre performance	OS1
Diameter	10.1 mm
Bending radius	>= 180 mm
Crush resistance	1800 N/m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.082 kg

Offer Sustainability

EU RoHS Directive	Compliant  EU RoHS Declaration
-------------------	---

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.