

Product data sheet

Characteristics

2F6CMOLDN

CBL FIB L/T DC 6 MMNY

Main

Product brand	Clipsal
Optic fiber type	Multi mode
Colour	White

Complementary

Optic fiber diameter	62.5/125 µm
Fibre performance	OM1
Diameter	5.6 mm
Bending radius	>= 105 mm
Crush resistance	600 N/m

Packing Units

Package 1 Weight	0.098 kg
------------------	----------

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Environmental Disclosure	 Product Environmental Profile

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.