

Product data sheet

Characteristics

2T100POJPP4

CBL 100PR 0.4MM EXT JF PE



Main

| | |
|------------------|------------------------|
| Product brand | Clipsal |
| Range of product | Actassi |
| Colour | External sheath: black |

Complementary

| | |
|---------------------------|--------------------------------------|
| Diameter | 0.4 mm conductor: |
| Cable stiffness | Solid class 1 |
| Number of conductors | 4 |
| Type of cable | 2 pairs with 4 conductor(s) stranded |
| Cable insulation material | PE (polyethylene) |
| External diameter | 5.4 mm |

Environment

| | |
|---------------------------------------|--|
| Environmental characteristic | Water resistant (radially) |
| Ambient air temperature for operation | -10...70 °C |
| Standards | AS/ACIF TS008 AS 1049-1 AS 1049-2 AS/NZS 1125 |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 0.548 kg |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |