

## Product data sheet

### Characteristics

# 2T100POJPP4

## Clipsal Actassi, External Jelly Filled Cables, Unscreened, Poly, 0.40mm, 100 Pair



### Main

Product brand	Clipsal
Range of product	Actassi
Colour	External sheath: black

### Complementary

Diameter	0.4 mm conductor:
Cable stiffness	Solid class 1
Number of conductors	4
Type of cable	2 pairs with 4 conductor(s) stranded
Cable insulation material	PE (polyethylene)
External diameter	5.4 mm

### Environment

Environmental characteristic	Water resistant (radially)
Ambient air temperature for operation	-10...70 °C
Standards	AS/ACIF TS008 AS 1049-1 AS 1049-2 AS/NZS 1125

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.548 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	<a href="#">RECh Declaration</a>
RECh free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>

