

Product data sheet

Characteristics

2T100POJPP4

CBL 100PR 0.4MM EXT JF PE



Main

Product brand	Clipsal
Range of product	Actassi
Colour	External sheath: black

Complementary

Diameter	0.4 mm conductor:
Cable stiffness	Solid class 1
Number of conductors	4
Type of cable	2 pairs with 4 conductor(s) stranded
Cable insulation material	PE (polyethylene)
External diameter	5.4 mm





Environment

Environmental characteristic	Water resistant (radially)
Ambient air temperature for operation	-10...70 °C
Standards	AS/ACIF TS008 AS 1049-1 AS 1049-2 AS/NZS 1125

Packing Units

Package 1 Weight	0.548 kg
------------------	----------

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	 RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile