

## Product data sheet

### Characteristics

# 2T25PIPV

## CBL 25PR 0.5MM PV/PV INT



### Main

Product brand	Clipsal
Range of product	Actassi
Cable shielding type	UTP
Colour	External sheath: cream

### Complementary

Diameter	0.5 mm conductor:
Cable stiffness	Solid class 1
Number of conductors	2
Cable insulation material	PE (polyethylene) PVC (polyvinyl chloride)
External diameter	10.6 mm

### Environment

Ambient air temperature for operation	-20...60 °C
Standards	ISO/IEC 11801 AS/NZS 3080 AS/ACIF S008

### Packing Units

Package 1 Weight	0.190 kg
------------------	----------

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>