

Product data sheet

Characteristics

2T2POJPE4

Clipsal Actassi, Lead in Cables, Jelly Filled Poly Jacket, 0.4, 2 Pair



Main

Product brand	Clipsal
Range of product	Actassi
Colour	External sheath: black



Complementary

Diameter	0.4 mm conductor:
Cable stiffness	Solid class 1
Number of conductors	4
Type of cable	2 pairs with 4 conductor(s) stranded
Cable insulation material	PE (polyethylene)
External diameter	4.6 mm



Environment

Environmental characteristic	Water resistant (radially)
Ambient air temperature for operation	-10...70 °C
Standards	AS/NZS 1125 AS 1049-1 AS 1049-2 AS/ACIF TS008

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	26 cm
Package 1 Width	34 cm
Package 1 Length	34 cm
Package 1 Weight	0.019 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
