

Product data sheet

Characteristics

2T50PIPV

CBL 50PR 0.5MM PV/PV INT



Main

| | |
|----------------------|------------------------|
| Product brand | Clipsal |
| Range of product | Actassi |
| Cable shielding type | UTP |
| Colour | External sheath: cream |

Complementary

| | |
|---------------------------|---|
| Diameter | 0.5 mm conductor: |
| Cable stiffness | Solid class 1 |
| Number of conductors | 2 |
| Cable insulation material | PE (polyethylene) PVC (polyvinyl chloride) |
| External diameter | 14.3 mm |

Environment

| | |
|---------------------------------------|--|
| Ambient air temperature for operation | -20...60 °C |
| Standards | ISO/IEC 11801 AS/NZS 3080 AS/ACIF S008 |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 0.343 kg |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| RECh Regulation | RECh Declaration |
| RECh free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |