

Product data sheet

Characteristics

2T50PIPV

Internal Telephone Cable, Clipsal Actassi, Unscreened, Plain PVC, 0.50, 50 Pair



Main

Product brand	Clipsal
Range of product	Actassi
Cable shielding type	UTP
Colour	External sheath: cream

Complementary

Diameter	0.5 mm conductor:
Cable stiffness	Solid class 1
Number of conductors	2
Cable insulation material	PE (polyethylene) PVC (polyvinyl chloride)
External diameter	14.3 mm

Environment

Ambient air temperature for operation	-20...60 °C
Standards	ISO/IEC 11801 AS/NZS 3080 AS/ACIF S008

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.343 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations