

Product data sheet

Characteristics

2T50PIPV

CBL 50PR 0.5MM PV/PV INT



Main

Product brand	Clipsal
Range of product	Actassi
Cable shielding type	UTP
Colour	External sheath: cream

Complementary

Diameter	0.5 mm conductor:
Cable stiffness	Solid class 1
Number of conductors	2
Cable insulation material	PE (polyethylene) PVC (polyvinyl chloride)
External diameter	14.3 mm

Environment

Ambient air temperature for operation	-20...60 °C
Standards	ISO/IEC 11801 AS/NZS 3080 AS/ACIF S008

Packing Units

Package 1 Weight	0.343 kg
------------------	----------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile