

Product data sheet

Characteristics

2T50POJPP4

Clipsal Actassi, External Jelly Filled Cables, Unscreened, Jelly Filled Poly, 50 Pair



Main

Product brand	Clipsal
Range of product	Actassi
Colour	External sheath: black

Complementary

Diameter	0.4 mm conductor:
Cable stiffness	Solid class 1
Number of conductors	4
Type of cable	2 pairs with 4 conductor(s) stranded
Cable insulation material	PE (polyethylene)
External diameter	14 mm


Environment

Environmental characteristic	Water resistant (radially)
Ambient air temperature for operation	-10...70 °C
Standards	AS/ACIF TS008 AS/NZS 1125 AS 1049-1 AS 1049-2

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.279 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations