

Product data sheet

Characteristics

30-WE

SWITCH 1 GANG ARCHITRAVE 1 WAY / 2 WAY 10A 250V



Main

Range of product	Standard Series
Product brand	Clipsal
Device presentation	Basic element with full cover plate and grid

Complementary

Switch function	1-pole
Number of rocker	1
Number of poles	1
Device mounting	Flush
Fixing mode	By screws
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	Without marking
Actuator	Rocker

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	3.3 cm
Package 1 Length	7.5 cm
Package 1 Weight	0.03 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	8.6 cm
Package 2 Width	7.1 cm
Package 2 Length	16.7 cm
Package 2 Weight	0.35 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	250
Package 3 Height	23.8 cm
Package 3 Width	34.2 cm
Package 3 Length	39 cm
Package 3 Weight	8.75 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile