

Product data sheet

Characteristics

30/2NM-WE

SWITCH MECH 1/2W 10A NEON



Main

Range of product	Standard Series Series 30
Product brand	Clipsal
Device presentation	Basic element

Complementary

Switch function	1-pole
Number of rocker	1
Number of poles	1
Device mounting	Flush
Material	PVC (polyvinyl chloride)
Surface finish	Glossy
Local signalling	neon
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Load type	Fluorescent 10 A LEDi lamp 100 W
Marking	Without marking
Actuator	Rocker

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.4 cm
Package 1 Width	2.5 cm
Package 1 Length	3.5 cm
Package 1 Weight	20 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	6.8 cm
Package 2 Width	5 cm
Package 2 Length	9.6 cm
Package 2 Weight	128 g
Unit Type of Package 3	CAR
Number of Units in Package 3	25
Package 3 Height	10.2 cm
Package 3 Width	12 cm
Package 3 Length	17 cm
Package 3 Weight	600 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile