

Product data sheet

Characteristics

3015C-VW

Clipsal Iconic, Single Power Point Skin, Horizontal Mount, 250V, 10A, Clip-On



Main

Range	Clipsal Iconic
Aesthetic name	Iconic
Product or component type	Cover frame
Colour tint	Vivid white (VW)
Type of packing	Polybag
Quantity per set	Set of 20

Complementary

Range compatibility	Clipsal Iconic switched socket
Product destination	Switched socket
Device mounting	Flush
Number of rocker	1
Number of power socket outlets	1
[In] rated current	10 A
Installation direction	Horizontal
Fixing mode	Clip-on
Surface finish	Matt
Surface treatment	Untreated
Material	PC (polycarbonate): skin ABS (acrylonitrile butadiene-styrene): skin
Height	120 mm
Width	78 mm
Depth	12 mm
Net weight	0.02 kg

Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1 cm
Package 1 Width	7.8 cm
Package 1 Length	12 cm
Package 1 Weight	23 g
Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Height	328 cm

Package 2 Width	106 cm
Package 2 Length	146 cm
Package 2 Weight	574.6 g
Unit Type of Package 3	PAL
Number of Units in Package 3	2400
Package 3 Height	950 cm
Package 3 Width	1140 cm
Package 3 Length	1140 cm
Package 3 Weight	55.2 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations