

## Product data sheet

### Characteristics

# 3015C-WY

Clipsal Iconic, cover frame, 1 switch & 1 socket, 10 A, Warm Grey



#### Main

Range	Clipsal Iconic
Aesthetic name	Iconic
Product or component type	Cover frame
Colour tint	Warm grey (WY)
Type of packing	Polybag
Quantity per set	Set of 20

#### Complementary

Range compatibility	Switched socket
Product destination	Switched socket
Device mounting	Flush
Number of rocker	1
Number of power socket outlets	1
[In] rated current	10 A
Installation direction	Horizontal
Fixing mode	Clip-on
Surface finish	Matt
Surface treatment	Untreated
Material	PC (polycarbonate): skin ABS (acrylonitrile butadiene-styrene): skin
Height	120 mm
Width	78 mm
Depth	12 mm
Net weight	0.02 kg

#### Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	21 g
Package 1 Height	12 mm
Package 1 width	78 mm
Package 1 Length	120 mm
Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Weight	574.6 g

Package 2 Height	328 mm
Package 2 width	106 mm
Package 2 Length	146 mm
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Weight	3258.2 g
Package 3 Height	335 mm
Package 3 width	261 mm
Package 3 Length	335 mm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>