

Product data sheet

Characteristics

3015XC-VW

Clipsal Iconic, cover frame, 2 switches & 1 socket, 10 A, Vivid White



Main

Range	Clipsal Iconic
Aesthetic name	Iconic
Product or component type	Cover frame
Colour tint	Vivid white (VW)
Type of packing	Polybag
Quantity per set	Set of 20

Complementary

Range compatibility	Switched socket
Product destination	Switched socket
Device mounting	Flush
Number of rocker	2
Number of power socket outlets	1
[In] rated current	10 A
Installation direction	Horizontal
Fixing mode	Clip-on
Surface finish	Matt
Surface treatment	Untreated
Material	PC (polycarbonate): skin ABS (acrylonitrile butadiene-styrene): skin
Height	120 mm
Width	78 mm
Depth	12 mm
Net weight	0.02 kg

Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	21.14 g
Package 1 Height	1.2 cm
Package 1 width	7.8 cm
Package 1 Length	12 cm
Unit Type of Package 2	CAR
Number of Units in Package 2	100
Package 2 Weight	3.322 kg

Package 2 Height	33.5 cm
Package 2 width	26.1 cm
Package 2 Length	33.5 cm
Unit Type of Package 3	BB1
Number of Units in Package 3	20
Package 3 Weight	587.4 g
Package 3 Height	32.8 cm
Package 3 width	10.6 cm
Package 3 Length	14.6 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile