

## Product data sheet

### Characteristics

# 3025/15C-VW

Clipsal Iconic, cover frame, 2 switches & 2 sockets, 15 A , Vivid White



#### Main

Range	Clipsal Iconic
Aesthetic name	Iconic
Product or component type	Cover frame
Colour tint	Vivid white (VW)
Type of packing	Polybag
Quantity per set	Set of 20

#### Complementary

Range compatibility	Switched socket
Product destination	Switched socket
Device mounting	Flush
Number of rocker	2
Number of power socket outlets	2
[In] rated current	15 A
Installation direction	Horizontal
Fixing mode	Clip-on
Surface finish	Matt
Surface treatment	Untreated
Material	PC (polycarbonate): skin ABS (acrylonitrile butadiene-styrene): skin
Height	120 mm
Width	78 mm
Depth	12 mm
Net weight	0.02 kg

#### Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	21.03 g
Package 1 Height	1.2 cm
Package 1 width	7.8 cm
Package 1 Length	12 cm
Unit Type of Package 2	CAR
Number of Units in Package 2	100
Package 2 Weight	3.311 kg

Package 2 Height	33.5 cm
Package 2 width	26.1 cm
Package 2 Length	33.5 cm
Unit Type of Package 3	BB1
Number of Units in Package 3	20
Package 3 Weight	585.2 g
Package 3 Height	32.8 cm
Package 3 width	10.6 cm
Package 3 Length	14.6 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>