

Product data sheet

Characteristics

3025VXUAG

Clipsal Iconic, switched socket, 2 switch & 2 socket, vert, 1 gang, 10 A



Main

Range	Clipsal Iconic
Product or component type	Switched socket
Device presentation	Mechanism with fixing frame
Outlet poles configuration	2P + E with shutter
Outlet standard	Australian

Complementary

Device mounting	Flush
Number of power socket outlets	2
Number of rocker	2
Range compatibility	Cover frame
Outlet standard description	With earthing contact
Outlet standard	Australian/New Zealand
Ground lug position	Straight 180° position
Number of gangs	1 gang
Fixing mode	By screw
Installation direction	Vertical
Colour	Ash grey
Surface finish	Matt
Type of packing	Polybag
Quantity per set	Set of 10
Sale per indivisible quantity	1
Rated current	10 A at 250 V AC 50 Hz
Electrical durability	12000 cycles
Connections - terminals	3 screw terminals
Screwdriver shape	Square drive no 1 (SQ1) Philips No 2
Clamping connection capacity	1 x 2.5...4 x 2.5 mm ² for rigid cable(s) 1 x 2.5...4 x 2.5 mm ² for stranded cable(s) 1 x 2.5...4 x 2.5 mm ² for flexible cable(s)
Wire stripping length	16 mm
Material	PC (polycarbonate): fixing frame PP (polypropylene): rocker POM (polyoxymethylene): shutter POM (polyoxymethylene): locking bar
Height	115 mm
Width	71 mm
Depth	31 mm
Embedding depth	24 mm
Product weight	0.094 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %
Standards	AS/NZS 3112
Product certifications	RCM

Packing Units

Package 1 Weight	93.000 g
Package 1 Height	40.000 mm
Package 1 width	72.000 mm
Package 1 Length	150.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile