

Product data sheet

Characteristics

3025XC-CY

Clipsal Iconic, Double Power Point Skin with 1 extra switch, Horizontal Mount, 250V, 10A, Clip-On



Main

| | |
|---------------------------|----------------|
| Range | Clipsal Iconic |
| Aesthetic name | Iconic |
| Product or component type | Cover frame |
| Colour tint | Cool grey (CY) |
| Type of packing | Polybag |
| Quantity per set | Set of 20 |

Complementary

| | |
|--------------------------------|---|
| Range compatibility | Clipsal Iconic switched socket |
| Product destination | Switched socket |
| Device mounting | Flush |
| Number of rocker | 3 |
| Number of power socket outlets | 2 |
| [In] rated current | 10 A |
| Installation direction | Horizontal |
| Fixing mode | Clip-on |
| Surface finish | Matt |
| Surface treatment | Untreated |
| Material | PC (polycarbonate): skin ABS (acrylonitrile butadiene-styrene): skin |
| Height | 120 mm |
| Width | 78 mm |
| Depth | 12 mm |
| Net weight | 0.02 kg |






Environment

| | |
|---------------------------------------|-----------|
| Ambient air temperature for operation | 0...45 °C |
| Relative humidity | 10...95 % |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 1.2 cm |
| Package 1 Width | 7.8 cm |
| Package 1 Length | 12 cm |
| Package 1 Weight | 21.32 g |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation |  REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant  EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| Sustainable packaging | Yes |
| China RoHS Regulation |  China RoHS Declaration |
| RoHS exemption information |  Yes |
| Environmental Disclosure |  Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |