

Product data sheet

Characteristics

3040CEP-VW

Clipsal Iconic, Cable Entry Plate, Horizontal Mount



Main

Range	Clipsal Iconic
Product or component type	Cable outlet
Device presentation	Complete product
Fixing mode	By screws

Complementary

Device mounting	Flush
Provided equipment	Skin Grid plate Seal
Cable entry	Flexible flaps
Outlet standard	Australian/New Zealand
Mounting mode	Horizontal
Colour tint	Vivid white
Surface finish	Matt
Type of packing	Polybag
Quantity per set	Set of 10
Ambient air temperature for storage	0...60 °C
Material	PC (polycarbonate): grid plate PP (polypropylene): flaps PP (polypropylene): cable flap
Height	78 mm
Width	120 mm
Depth	20 mm
Net weight	0.061 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.0 cm
Package 1 Width	10.1 cm
Package 1 Length	17.8 cm
Package 1 Weight	0.016 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information