

## Product data sheet

### Characteristics

# 3041HA-VW

## Clipsal Iconic Flush Switch, Horizontal Mount, 1 Gang, 1 Way/2 Way, 250V 10AX



### Main

Range	Clipsal Iconic
Product or component type	Switch
Device application	Lighting
Load type	Fluorescent 10 A LEDi lamp 100 W
Colour tint	Vivid white
Quantity per set	Set of 20

### Complementary

Device presentation	Complete product
Control type	Rocker
Device mounting	Flush
Installation direction	Horizontal
Switch function	1-pole 1/2-way
Number of rocker	1
Rated current	10 A
[Ue] rated operational voltage	250 V
Material	Plastic
Height	78 mm
Width	120 mm
Depth	39 mm
Net weight	0.078 kg

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.9 cm
Package 1 Width	8.3 cm
Package 1 Length	12.5 cm
Package 1 Weight	75.12 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	328 cm
Package 2 Width	106 cm
Package 2 Length	146 cm
Package 2 Weight	0.972 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>