

Product data sheet

Characteristics

3041V44-VW

Clipsal Iconic, switch, vertical, IP 44, 10 A, Vivid White



Main

Range	Clipsal Iconic
Product or component type	Switch
Device application	Lighting
Colour tint	Vivid white
Quantity per set	Set of 20

Complementary

Device presentation	Complete product
Control type	Rocker
Device mounting	Flush
Installation direction	Vertical
Switch function	1-pole 1/2-way
Number of rocker	1
Rated current	10 A
[Ue] rated operational voltage	250 V
Material	Plastic
Height	124 mm
Width	82 mm
Depth	40 mm
Net weight	0.098 kg

Environment

IP degree of protection	IP44
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	80.0 g
Package 1 Height	3.9 cm
Package 1 width	7.8 cm
Package 1 Length	12 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	964.6 g
Package 2 Height	32.8 cm
Package 2 width	10.6 cm
Package 2 Length	14.6 cm
Unit Type of Package 3	CAR

Number of Units in Package 3	50
Package 3 Weight	5.208 kg
Package 3 Height	33.5 cm
Package 3 width	26.1 cm
Package 3 Length	33.5 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile