

Product data sheet

Characteristics

3041VA-VW

Clipsal Iconic, Flush Switch, Vertical Mount, 1 Gang, 250V, 10Ax1-Way/2-Way



Main

Range	Clipsal Iconic
Product or component type	Switch
Device application	Lighting
Load type	Fluorescent 10 A LEDi lamp 100 W
Colour tint	Vivid white
Quantity per set	Set of 20

Complementary

Device presentation	Complete product
Control type	Rocker
Device mounting	Flush
Installation direction	Vertical
Switch function	1-pole 1/2-way
Number of rocker	1
Rated current	10 A
[Ue] rated operational voltage	250 V
Material	Plastic
Height	120 mm
Width	78 mm
Depth	39 mm
Net weight	0.078 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.9 cm
Package 1 Width	8.3 cm
Package 1 Length	12.5 cm
Package 1 Weight	75.12 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	150 cm
Package 2 Width	110 cm
Package 2 Length	330 cm
Package 2 Weight	0.962 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Height	335 cm
Package 3 Width	261 cm

Package 3 Length	335 cm
Package 3 Weight	4964.2 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile