

## Product data sheet

### Characteristics

# 3041VAG

## Clipsal Iconic Gridplate and Mechanism, 1 Gang, 250V, 10AX



### Main

Range of product	Iconic
Range of product	Clipsal Iconic
Aesthetic name	Iconic
Product or component type	Switch
Product brand	Clipsal
Device application	Switching loads
Device presentation	Complete product
Provided equipment	Switch
Colour	White (-)
Type of packing	Bag
Quantity per set	1
Sale per indivisible quantity	1
Motor M-rating AS3133	M80
Load type	Fluorescent 10 AX LED lamp 100 W

### Complementary

Technology type	Electromechanical
Switch pattern	[1]
Switch application	On/off switching
Device mounting	Flush
Switch function	1-pole 1/2-way
[Ue] rated operational voltage	250 V
Number of modules	1 module
Number of gangs	1 gang
Number of rocker	1
Actuator	Rocker
Product destination	Rocker switch
Range compatibility	Iconic
Connections - terminals	Screw terminal
Surface treatment	Plastic coated
Rated current	10 AX at 250 V AC
Local signalling	Without light indicator
Material	Plastic: rocker
Height	120 mm
Width	78 mm
Depth	39 mm

### Environment

Standards	AS/NZS 3133
IP degree of protection	IP20

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	7.1 cm
Package 1 Length	11.5 cm
Package 1 Weight	0.06 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>