

Product data sheet

Characteristics

3041VH-VW

Clipsal Iconic, Gridplate and Skin, 1 Gang, Vertical/Horizontal



Main

Range	Clipsal Iconic
Aesthetic name	Iconic
Product or component type	Cover frame
Colour tint	Vivid white (VW)
Type of packing	Polybag
Quantity per set	Set of 20

Complementary

Range compatibility	Clipsal Iconic switch
Product destination	Switch
Number of rocker	1
Device composition	Fixing frame
Installation direction	Horizontal/vertical
Fixing mode	Screw
Surface finish	Matt
Surface treatment	Untreated
Material	PC (polycarbonate): grid plate PP (polypropylene): flaps POM (polyoxymethylene): locking bar PC (polycarbonate): skin ABS (acrylonitrile butadiene-styrene): skin
Height	120 mm
Width	78 mm
Depth	7.5 mm
Embedding depth	15 mm
Net weight	0.04 kg

Environment

Ambient air temperature for storage	0...60 °C
Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.2 cm
Package 1 Width	8.4 cm
Package 1 Length	13.6 cm
Package 1 Weight	68 g
Unit Type of Package 2	BB1

Number of Units in Package 2	15
Package 2 Height	150 cm
Package 2 Width	108 cm
Package 2 Length	330 cm
Package 2 Weight	1.146 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	75
Package 3 Height	335 cm
Package 3 Width	261 cm
Package 3 Length	335 cm
Package 3 Weight	5.1 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile