

## Product data sheet

### Characteristics

# 3042HAL-VW

Clipsal Iconic, Flush Switch, Horizontal Mount, 2 Gang, 250V, 10AX, LED



#### Main

Range	Clipsal Iconic
Product or component type	Switch
Device application	Lighting
Load type	Fluorescent 10 A LEDi lamp 100 W
Colour tint	Vivid white
Quantity per set	Set of 20

#### Complementary

Device presentation	Complete product
Control type	Rocker
Device mounting	Flush
Installation direction	Horizontal
Switch function	1-pole 1/2-way
Number of rocker	2
Local signalling	LED indicator
Rated current	10 A
[Ue] rated operational voltage	250 V
Material	Plastic
Height	78 mm
Width	120 mm
Depth	39 mm
Net weight	0.092 kg

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	7.6 cm
Package 1 Length	13.2 cm
Package 1 Weight	104 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	148 cm
Package 2 Width	108 cm
Package 2 Length	332 cm
Package 2 Weight	1.254 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	1200
Package 3 Height	950 cm

Package 3 Width	1140 cm
Package 3 Length	1140 cm
Package 3 Weight	124.8 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations