

Product data sheet

Characteristics

3042V44-VW

Switch, Clipsal Iconic, Vertical 2 Gang, 1/2 Way
10AX,230/240V, IP44



Main

Range	Clipsal Iconic
Product or component type	Switch
Device application	Lighting
Colour tint	Vivid white
Quantity per set	Set of 20

Complementary

Device presentation	Complete product
Control type	Rocker
Device mounting	Flush
Installation direction	Vertical
Switch function	1-pole 1/2-way
Number of rocker	2
Rated current	10 A
[Ue] rated operational voltage	230/240 V
Material	Plastic
Height	124 mm
Width	82 mm
Depth	40 mm
Net weight	0.098 kg

Environment

IP degree of protection	IP44
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.502 cm
Package 1 Width	7.78 cm
Package 1 Length	12.02 cm
Package 1 Weight	98 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	32.8 cm
Package 2 Width	10.6 cm
Package 2 Length	14.6 cm
Package 2 Weight	1.145 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations