

## Product data sheet

### Characteristics

# 3042V44-VW

Clipsal Iconic, 2 switches, vertical, IP44, 10 A, vivid white



#### Main

Range	Clipsal Iconic
Product or component type	Switch
Device application	Lighting
Colour tint	Vivid white
Quantity per set	Set of 20

#### Complementary

Device presentation	Complete product
Control type	Rocker
Device mounting	Flush
Installation direction	Vertical
Switch function	1-pole 1/2-way
Number of rocker	2
Rated current	10 A
[Ue] rated operational voltage	250 V
Material	Plastic
Height	124 mm
Width	82 mm
Depth	40 mm
Product weight	0.098 kg

#### Environment

IP degree of protection	IP44
-------------------------	------

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	98 g
Package 1 Height	35.02 mm
Package 1 width	77.8 mm
Package 1 Length	120.2 mm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	1144.6 g
Package 2 Height	328 mm
Package 2 width	106 mm
Package 2 Length	146 mm
Unit Type of Package 3	CAR

Number of Units in Package 3	50
Package 3 Weight	6108.2 g
Package 3 Height	335 mm
Package 3 width	261 mm
Package 3 Length	335 mm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>