

## Product data sheet

### Characteristics

# 3042VH-VW

## Clipsal Iconic, Gridplate and Skin, 2 Gang, Vertical/Horizontal



### Main

Range	Clipsal Iconic
Aesthetic name	Iconic
Product or component type	Cover frame
Colour tint	Vivid white (VW)
Type of packing	Polybag
Quantity per set	Set of 20

### Complementary

Range compatibility	Clipsal Iconic switch
Product destination	Switch
Device mounting	Flush
Number of rocker	2
Device composition	Fixing frame
Installation direction	Horizontal/vertical
Fixing mode	Screw
Surface finish	Matt
Surface treatment	Untreated
Material	PC (polycarbonate): grid plate PP (polypropylene): flaps POM (polyoxymethylene): locking bar PC (polycarbonate): skin ABS (acrylonitrile butadiene-styrene): skin
Height	120 mm
Width	78 mm
Depth	7.5 mm
Embedding depth	15 mm
Net weight	0.04 kg

### Environment

Ambient air temperature for storage	0...60 °C
Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.1 cm
Package 1 Width	15.2 cm
Package 1 Length	8.5 cm
Package 1 Weight	70 g

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>