

Product data sheet

Characteristics

3043USBG

Clipsal Iconic, USB Charger Grid and Module, 3 Gang



Main

Range	Clipsal Iconic
Product or component type	USB charger
[Ue] rated operational voltage	220/240 V AC 50 Hz
Integrated connection type	3 USB 2.0 type A 5 V DC, maximum load current: 2.1 A
Maximum load current with 2 outputs used simultaneously	4.5 A

Complementary

Device mounting	Flush
Device presentation	Mechanism with fixing frame
Colour tint	Vivid white
Surface finish	Matt Textured
Fixing mode	By screws
Type of packing	Polybag
Sale per indivisible quantity	1
Ambient air temperature for operation	0...35 °C
Ambient air temperature for storage	0...60 °C
Relative humidity	5...90 %
Protection type	Short time short-circuit protection
Number of terminals	3 screw terminal
Screwdriver shape	Philips No 2 Square drive no 1 (SQ1)
Clamping connection capacity	4 x 2.5 mm ² for stranded cable(s) 4 x 2.5 mm ² for flexible cable(s) 4 x 2.5 mm ² for rigid cable(s)
Wire stripping length	10 mm
Height	71 mm
Width	5 mm
Depth	5 mm
Embedding depth	35 mm





Environment

Product certifications	RCM
------------------------	-----

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4 cm
Package 1 Width	7.1 cm
Package 1 Length	11.6 cm
Package 1 Weight	123 g

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes