

## Product data sheet

### Characteristics

# 3043V44-VW

## Clipsal Iconic, Switch, Vertical 3 Gang, 1/2 Way 10AX, 250V, IP44



### Main

Range	Clipsal Iconic
Product or component type	Switch
Device application	Lighting
Load type	Fluorescent 10 A LEDi lamp 100 W
Colour tint	Vivid white
Quantity per set	Set of 20

### Complementary

Device presentation	Complete product
Control type	Rocker
Device mounting	Flush
Installation direction	Vertical
Switch function	1-pole 1/2-way
Number of rocker	3
Rated current	10 A
[Ue] rated operational voltage	250 V
Material	Plastic
Height	124 mm
Width	82 mm
Depth	40 mm
Net weight	0.098 kg

### Environment

IP degree of protection	IP44
-------------------------	------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.94 cm
Package 1 Width	7.78 cm
Package 1 Length	12.02 cm
Package 1 Weight	110 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	32.8 cm
Package 2 Width	10.6 cm
Package 2 Length	14.6 cm
Package 2 Weight	1.265 kg
Unit Type of Package 3	CAR

Number of Units in Package 3	50
Package 3 Height	33.5 cm
Package 3 Width	26.1 cm
Package 3 Length	33.5 cm
Package 3 Weight	6.708 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>