Product data sheet
Characteristics

3043V44-VW
Clipsal Iconic, Switch, Vertical 3 Gang, 1/2 Way 10AX, 250V, IP44

Main

Range	Clipsal Iconic
Product or component type	Switch
Device application	Lighting
Load type	Fluorescent 10 A LEDi lamp 100 W
Colour tint	Vivid white
Quantity per set	Set of 20

Complementary

Device presentation	Complete product
Control type	Rocker
Device mounting	Flush
Installation direction	Vertical
Switch function	1-pole 1/2-way
Number of rocker	3
Rated current	10 A
[Ue] rated operational voltage	230/240 V
Material	Plastic
Height	124 mm
Width	82 mm
Depth	40 mm
Net weight	0.098 kg

Environment

IP degree of protection	IP44

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.94 cm
Package 1 Width	7.78 cm
Package 1 Length	12.02 cm
Package 1 Weight	110 g

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACh Regulation	REACh Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations