

Product data sheet

Characteristics

3043VH-VW

Gridplate and Skin, Clipsal Iconic, 3 Gang, Vertical/Horizontal

Main

Range	Clipsal Iconic
Aesthetic name	Iconic
Product or component type	Cover frame
Colour tint	Vivid white (VW)
Type of packing	Polybag
Quantity per set	Set of 20

Complementary

Range compatibility	Clipsal Iconic USB charger
Product destination	USB charger
Device mounting	Flush
Number of rocker	3
Device composition	Fixing frame
Installation direction	Horizontal/vertical
Fixing mode	Screw
Surface finish	Matt
Surface treatment	Untreated
Material	PC (polycarbonate): grid plate PP (polypropylene): flaps POM (polyoxymethylene): locking bar PC (polycarbonate): skin ABS (acrylonitrile butadiene-styrene): skin
Height	120 mm
Width	78 mm
Depth	7.5 mm
Embedding depth	15 mm
Net weight	0.04 kg

Environment

Ambient air temperature for storage	0...60 °C
Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.4 cm
Package 1 Width	8.5 cm
Package 1 Length	14.8 cm
Package 1 Weight	68.0 g

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	Yes
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Take-back	No
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	1