

## Product data sheet

### Characteristics

# 3044VA-VW

## Clipsal Iconic Flush Switch, Vertical Mount, 4 Gang, 250V, 10Ax1 Way/2 Way



### Main

|                           |                                     |
|---------------------------|-------------------------------------|
| Range                     | Clipsal Iconic                      |
| Product or component type | Switch                              |
| Device application        | Lighting                            |
| Load type                 | Fluorescent 10 A<br>LEDi lamp 100 W |
| Colour tint               | Vivid white                         |
| Quantity per set          | Set of 20                           |

### Complementary

|                                |                  |
|--------------------------------|------------------|
| Device presentation            | Complete product |
| Control type                   | Rocker           |
| Device mounting                | Flush            |
| Installation direction         | Vertical         |
| Switch function                | 1-pole 1/2-way   |
| Number of rocker               | 4                |
| Rated current                  | 10 A             |
| [Ue] rated operational voltage | 250 V            |
| Material                       | Plastic          |
| Height                         | 120 mm           |
| Width                          | 78 mm            |
| Depth                          | 39 mm            |
| Net weight                     | 0.124 kg         |

### Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type of Package 1       | PCE      |
| Number of Units in Package 1 | 1        |
| Package 1 Height             | 4.6 cm   |
| Package 1 Width              | 9 cm     |
| Package 1 Length             | 13.7 cm  |
| Package 1 Weight             | 132 g    |
| Unit Type of Package 2       | BB1      |
| Number of Units in Package 2 | 10       |
| Package 2 Height             | 148 cm   |
| Package 2 Width              | 106 cm   |
| Package 2 Length             | 330 cm   |
| Package 2 Weight             | 1.442 kg |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product                         |
| REACH Regulation           | <a href="#">REACH Declaration</a>             |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a> |
| Mercury free               | Yes   |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>        |
| RoHS exemption information | <a href="#">Yes</a>                           |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a> |